



COLONNA DI GUIDA A UN DIAMETRO


GUIDE PILLAR WITH OIL GROOVES

FÜHRUNGSBOLZEN MIT SCHMIERNUTEN

ECO-2

Acciaio: Da cementazione
Steel: Case hardened
Stahl: Einsatzhärtung

Durezza: HRC 60-62
Hardness: HRC 60-62
Härte: HRC 60-62



D1	D2	K	L2	L1	L			
12	16	5	5	12,5	50			
				15	60			
				17,5	70			
				20	80			
				22,5	90			
				25	100			
				27	120	140		
14	18	5	5	12,5	50			
				15	60			
				17,5	70			
				20	80			
				22,5	90			
				25	100			
				27	120	140		
16	20	5	5	12,5	50			
				15	60			
				17,5	70			
				20	80			
				22,5	90			
				25	100			
				27	120	140		
18	22	5	5,5	12,5	50			
				15	60			
				17,5	70			
				20	80			
				22,5	90			
				25	100			
				27	120			
20	24	6	6	15	60			
				17,5	70			
				20	80			
				22,5	90			
				25	100			
				27	120			
				30	140	160	180	
50	200							

D1	D2	K	L2	L1	L			
25	30	7	7	20	80			
				22,5	90			
				25	100			
				27	120			
				30	140	160	180	
				50	200	220	240	
				55	260	280		
32	37	7	7,5	30	120			
				35	140			
				40	160			
				45	180			
				50	200	220	240	
				55	260	280		
				60	300			
40	45	8	8	30	120			
				35	140			
				40	160			
				45	180			
				50	200	220	240	
				55	260	280		
				60	300			
50	55	10	9	55	260	280		
				60	300			
				70	350			
				80	400	450		
				100	500			
				120	600			
				140	800			
60	68	12	10	70	350			
				80	400	450		
				100	500			
				120	600			
				140	800			

Esempio di ordinativo: D1xL **Order example:** D1xL **Bestellbeispiel:** D1xL